





**VIRAJ 5690
DAISY CURVE**

divinity lights





Lens



VIRAJ 5690 DAISY CURVE

Viraj 5690 Daisy Curve has:

- Extruded Aluminium Luminaire Housing
- Premium Finish Powder coating
- Snap-fit system with No visible screw
- Unique lens System
- 3 beam angle options 30°, 50° and widespread 80°
- Energy efficient LED with high colour rendering
- LED PCB mounted on insert design with heat sink
- Pendant using suspension cable with M6 bolt and fastener
- Bottom opening for easy maintenance

Quick Info

CRI ≥90
 3000K/ 4000K/ 5700K
 TUNABLE WHITE 2700-6500K
 ON-OFF/ ON-OFF (FLICKER FREE)
 DALI-2 DT6 / DALI-2 DT8/ DALI+
 SDCM<3
 Lens
 L70 @50,000h
 Aluminium


Types

Pendant/ Surface


Single Line Diagram

Pendant/Surface Mounted

Outer Profile Code
 SY-107




Profile Insert Code
 SY-106



Light Distribution

Direct Direct-Indirect



CRI ≥ 90



TUNABLE
 WHITE

VIRAJ 5690 CURVE DAISY



VIRAJ 5690 DAISY CURVE (DIRECT)

System Power	Dimensions
7W	L = 300mm
14W	L = 600mm
21W	L = 900mm
28W	L = 1200mm
56W	L = 2400mm

VIRAJ 5690 DAISY CURVE (DIRECT-INDIRECT)

System Power	Dimensions
9W	L = 300mm
18W	L = 600mm
27W	L = 900mm
35W	L = 1200mm
70W	L = 2400mm

Order Options

Distribution

- Direct
- Indirect
- Up-50% / Down-50%
- Up-30% / Down-70%
- Up-70% / Down-30%
- Up-20% / Down-80%
- Up-80% / Down-20%

CCT (Color Temperature)

- 3000K
- 4000K
- 5700K
- Tunable 2700K-6500K



CRI

>90

Beam Angle

78°

Control

- ON-OFF
- ON-OFF (FLICKER FREE)
- DALI-2 DT6
- DALI-2 DT8
- DALI +




Mounting Type

- Pendent
- Surface
- Recessed

Material Color


RAL As Per Request

Photometric Details




PHOTOMETRIC DETAILS

DAISY-7X1-BW




~80° batwing beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W




~50° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W-D




~50° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips.

DAISY-7X1-O-D




~25 + 70° oval beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-M




~35° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-FT-D




Forward throwing beam for freestanding office luminaires. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WW




~80° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WW-D




~80° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-O




~25 + 70° oval beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WAS




Asymmetric Beam for Wall-Washing

DAISY-7X1-M-D




~35° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W2




~50° wide beam with tighter cutoff. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W2-D




~50° wide beam with tighter cutoff. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-ZT25



Asymmetric beam for aisle lighting. Clear version for high contrast lighting. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-ZT25-D



Asymmetric beam for aisle lighting. Diffused version for perfect colour mixing. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.