


**VIRAJ DAISY
MINI**

divinity lights



Quick Info

CRI ≥90

3000K/ 4000K/ 5700K

TUNABLE WHITE 2700-6500K

ON-OFF/ ON-OFF (FLICKER FREE)

DALI-2 DT6 / DALI-2 DT8/ DALI+

SDCM<3

Lens

L70 @50,000h

Aluminium

Types


Pendant/ Surface/ Recessed

Single Line Diagram

Pendant/Surface Mounted

Profile Code


SY-146



Profile Code


SY-108

Recessed Mounted



Light Distribution


Direct



CRI ≥ 90



TUNABLE
WHITE



Lens



VIRAJ DAISY MINI

Viraj Daisy Mini sleek and slim linear fixture has :

- Extruded Aluminium Luminaire Housing
- Premium Finish Powder coating
- Snap- fit system with No visible screw
- Unique lens System
- 3 beam angle options 30°, 55° and widespread 65°
- Energy efficient LED with high colour rendering
- LED PCB mounted on insert design with heat sink
- Pendant using suspension cable with M6 bolt and fastener
- Bottom opening for easy maintenance

VIRAJ DAISY MINI



VIRAJ DAISY MINI (DIRECT)

System Power	Dimensions
6W	L = 300mm
12W	L = 600mm
18W	L = 900mm
25W	L = 1200mm
50W	L = 2400mm

Order Options

Distribution

- Direct
- Indirect
- Up-50% / Down-50%
- Up-30% / Down-70%
- Up-70% / Down-30%
- Up-20% / Down-80%
- Up-80% / Down-20%

CCT (Color Temperature)

- 3000K
- 4000K
- 5700K
- Tunable 2700K-6500K



CRI

>90

Beam Angle

78°

Control

- ON-OFF
- ON-OFF (FLICKER FREE)
- DALI-2 DT6
- DALI-2 DT8
- DALI +




Mounting Type

- Pendent
- Surface
- Recessed

Material Color


RAL As Per Request

Photometric Details




PHOTOMETRIC DETAILS

DAISY-7X1-BW




~80° batwing beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W




~50° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W-D




~50° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips.

DAISY-7X1-O-D




~25 + 70° oval beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-M




~35° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-FT-D




Forward throwing beam for freestanding office luminaires. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WW




~80° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WW-D




~80° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-O




~25 + 70° oval beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WAS




Asymmetric Beam for Wall-Washing

DAISY-7X1-M-D




~35° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W2




~50° wide beam with tighter cutoff. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W2-D




~50° wide beam with tighter cutoff. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-ZT25



Asymmetric beam for aisle lighting. Clear version for high contrast lighting. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.


DAISY-7X1-ZT25-D



Asymmetric beam for aisle lighting. Diffused version for perfect colour mixing. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.


BEAM ANGLE OPTION

DAISY-MINI-W




~55° wide beam

DAISY-MINI-W-D




~55° wide beam. Variant with diffused lenses.

DAISY-MINI-FT-D




Forward throwing beam for freestanding office luminaires

DAISY-MINI-M




~40° wide beam. Variant with diffused lenses.

DAISY-MINI-M-D




~65° extra wide beam. Variant with diffused lenses.

DAISY-MINI-WWW-D




~65° extra wide beam. Variant with diffused lenses.

DAISY-MINI-WW



~65° wide beam

DAISY-MINI-WW-D



~65° wide beam. Variant with diffused lenses.